



**Set SI 1100**  
for EBI 12 and EBI 11

- 2-port Interface IF 100
- Software Winlog.pro
- USB connection
- Colored LEDs signaling programming, readout and incorrect development



**Set SI 1200**  
for EBI 12

- 4-port Interface IF 200
- Software Winlog.pro
- USB connection
- Colored LEDs signaling programming, readout and incorrect development
- Includes antenna



**Set SI 2100**  
for EBI 12 and EBI 11

- 2-port Interface IF 100
- Software Winlog.med
- USB connection
- Colored LEDs signaling programming, readout and incorrect development



**Set SI 2110**  
for EBI 12

- 4-port Interface IF 200
- Software Winlog.med
- USB connection
- Colored LEDs signaling programming, readout and incorrect development
- Includes antenna



**Set SI 2150**  
for EBI 12 and EBI 16

- 1-port Interface IF 150
- Software Winlog.med
- USB connection
- Colored LEDs signaling programming, readout and incorrect development



**Set SI 3200**  
for EBI 12

- 4-port Interface IF 200
- Software Winlog.validation
- USB connection
- Colored LEDs signaling programming, readout and incorrect development
- Includes antenna



**AL 112**  
for IF100 and IF 200

- Developed for real time monitoring
- AL 112 is a cable with 3 m length
- Antenna placement in the field of the door seal of a sterilizer or washer-disinfector
- Antenna steam-tight
- It is possible by a sealing to introduce it in the chamber



**Can adapter set**  
**EBI DA-Set**

With this adapter set you can fix the data loggers at cans or plastic bags. Designed for data loggers of the EBI 12 series with axial, radial or external probes. Hereby you assure the use to ensure proper probes placement.