Service cables

For HF, HP21 / 22, HL-20

FEATURES

Service cables

Order code

AC3006

- Connects Rotronic instruments via their service interface (UART) to a USB interface
- Requires HW4 software
- For programming (settings, scaling, firmware update, etc.)

Description

• Two different types: AC3006, the instrument must be supplied with power. AC3009, the instrument is supplied with power via the USB interface.

Service cable without power supply

AC3006 in combination with a 2-wire type: with all 2-wire types (HF320, HF420, HF520, HF620, HF720) ensure that the computer or laptop is galvanically isolated from the main power supply.



rotro





AC3009

Length

1.8 m



AC3006 / AC3009



AC3009	Service cable with power	3.6 m	
	AC3006	AC3009	AC0006
HF1			
HF3	\checkmark	\checkmark	
HF4	\checkmark	\checkmark	
HF5	\checkmark	\checkmark	
HF7	\checkmark	\checkmark	
HF8	\checkmark	\checkmark	
TF5	\checkmark	\checkmark	
PF4	\checkmark	\checkmark	
PF5	\checkmark	\checkmark	
HL-20	1	\checkmark	
HL-NT			
BL-1D			
HL-1D			
TL-1D			
CL11			
HP21	\checkmark	\checkmark	
HP32			\checkmark
HP23			
TP22	1	\checkmark	
CP11			
AwTherm			\checkmark
HygroLab C1		\checkmark	
CRP1	\checkmark		
CRP5	\checkmark		

2020-V2