Pressure gauge per EN 837-1 with mounted diaphragm seal For sanitary applications Model DSS19F, with SMS threaded connection

WIKA data sheet DS 95.21

Applications

- Hygienic pressure measurement in sanitary applications for the food and beverage industry
- Mechanical pressure display on pipelines and vessels
- For gases, vapour; liquid, pasty, powdery and crystallising media

Special features

- Quick cleaning, without residue
- Threaded connection per SMS standard (SS 3352)
- Suitable for cleaning out of place (COP)



Diaphragm seal system, model DSS19F

Description

Diaphragm seal systems are used to protect the pressure measuring instrument from aggressive, adhesive, crystallising, corrosive, highly viscous, environmentally hazardous or toxic media. The diaphragm made of stainless steel provides for the separation from the medium. The pressure is transmitted to the measuring instrument via the system fill fluid which is inside the diaphragm seal system.

The DSS19F complies with all requirements of the food industry. The threaded connection enables a hygienic process connection.

The requirements of COP (cleaning out of place) are fulfilled.


The diaphragm seal systems can withstand the cleaning vapour temperatures occurring in the SIP processes and thus ensure a sterile connection between the medium to be measured and the diaphragm seal.

The diaphragm seal is directly welded to the measuring instrument.

The DSS19F is used for pressure measurement in various process steps, e.g. filtration, separation, pasteurisation, and in filling systems.

WIKA data sheet DS 95.21 · 05/2017

Page 1 of 4





Specifications


Model DSS19F					
Design	Pressure gauge with Bourdon tube per EN 837-1, welded to diaphragm seal				
Nominal size (NS)	100				
Accuracy class	1.0				
Pressure limitation	Steady:Full scale valueFluctuating:0.9 x full scale valueShort time:1.3 x full scale value				
Permissible temperature range Medium Ambient Storage	10 80 °C (50 176 °F) for SIP and CIP max. 130 °C (266 °F) 10 40 °C (50 104 °F) 10 60 °C (50 140 °F)				
Ingress protection	IP65 per IEC/EN 60529				
Material wetted non-wetted	Upper body of diaphragm seal: Stainless steel 1.4435 (316L) Diaphragm of diaphragm seal: Stainless steel 1.4435 (316L) Case: Stainless steel 1.4301 (304) Window: Laminated safety glass Dial, pointer: Aluminium				
Surface roughness wetted non-wetted	Ra \leq 0.76 μm (30 μin) per ASME BPE SF3 (except for weld seam) Case: Ra \leq 0.76 μm (30 μin) (except for weld seam)				
Level of cleanliness of wetted parts	Oil and grease free per ASTM G93-03 level E (WIKA standard) and ISO 15001 (< 550 mg/m ²)				
System fill fluid	Medicinal white mineral oil KN 92 (FDA 21 CFR 172.878, 21 CFR 178.3620(a); USP, EP, JP), recom- mendation for pharmaceutical and cosmetics applications				

Measuring ranges in bar (psi)


Gauge pressure								
0 1 (0 15)	0 1.6 (0 25)	0 2.5 (0 40)	0 4 (0 60)					
0 6 (0 100)	0 10 (0 160)	0 16 (0 250)	0 25 (0 300)					

Vacuum and +/- measuring range							
-1 +5 (-30 inHg +70)	-1 +9 (-30 inHg +130)	-1 +10 (-30 inHg +145)					

Model DSS19F illustrated on a pipe socket



Dimensions in mm (in)



Type of process connection: SMS threaded connection Pipe standard: Threaded connection per SMS standard (SS 3352)

DN	For pipe Outer Ø x wall thickness	PN	Dimensions in mm (in)					
			NG	G	н	D	d ₂	Mb
1 1⁄2"	38 x 1.2 (1.102 x 0.047)	40	100 (3.937)	RD 60 x 1/6 (2.362 x 1/6)	120 (4.724)	74 (2.913)	55 (2.165)	35 (1.378)
2"	51 x 1.2 (2.008 x 0.059)	40	100 (3.937)	RD 70 x 1/6 (2.756 x 1/6)	120 (4.724)	84 (3.307)	65 (2.559)	45 (1.772)

Certificates (option)

- 3.1 inspection certificate per EN 10204 (e.g. material proof for wetted metallic parts, calibration certificate)
- 3.1 calibration certificate (list of single measured values;
 5 measuring points)

Approvals and certificates, see website

Ordering information

Scale range / Process connection (type of process connection, pipe standard, pipe dimension) / Material of wetted parts / Certificates

© 05/2017 WIKA Alexander Wiegand SE & Co. KG, all rights reserved. The specifications given in this document represent the state of engineering at the time of publishing. We reserve the right to make modifications to the specifications and materials.

Page 4 of 4

WIKA data sheet DS 95.21 · 05/2017



WIKA Alexander Wiegand SE & Co. KG Alexander-Wiegand-Straße 30 63911 Klingenberg/Germany Tel. +49 9372 132-0 Fax +49 9372 132-406 info@wika.de www.wika.de